

MTS / T-BERD 6000

WITH SN > 10 000

MTS / T-BERD 6000A

B14054

RELEASE NOTE

Ste-Core Package 14054 (January 2014)

- Boot V5.00 (30/Jan/2014)
- Linux Kernel V6.50 (30/Jan/2014)
- File System V4.62 (30/Jan/2014)
- Instrument Setup V12.60 (30/Jan/2014)
- Microscope V12.60 (30/Jan/2014)

Ste-Optical Package 14054 (January 2013)

- Fiber Optics V12.60 (30/Jan/2014)

(This release note supersedes the previous B13514 and B14024 release notes).

CONTENTS

T-BERD/MTS 6000/6000A Base Unit	3
Improvements	3
FO Functions	3
Improvements	3
OTDR	3
New functionalities	3
Improvements	3
OSA	4
Improvements	4
FiberComplete	4
New functionalities	4
Improvements	4
Scope	4
Improvements	4
Script	4
New functionalities	4

T-BERD/MTS 6000/6000A Base Unit

Improvements

- Improved management of the datalink
- Improved management of the battery level and low battery indication
- Better management of the text editor
- Improved management of the PDF editor (larger font provided)
- Improved management of the VFL
- Improved management of 8A battery type (not part of previous B13514 release)
- Improved format process for extended memory (not part of previous B13514 release)
- Better management of the 3G/4G USB dongle (not part of previous B14024 release)

FO Functions

Improvements

- Color coding with up to 6 digits for numbers

OTDR

New functionalities

- Management of merged events

Improvements

- For the OEO tab, use the same setup organization than for the standard OTDR tab
- With the OEO tab, when changing the file type, there is no longer the disappearance of the trace selection on the result page
- Improved management of traffic detection
- Improved management of the alarms for Expert and FTTH-SLM modes
- Improvement on the refresh of cable Id when using different extremities and changing the direction
- Improved report with OptiPulses traces
- Improved management of the Optipulses licence
- For FTTH-SLM and FTTA-SLM, the real time no longer modifies the acquisition configuration settings
- Improved automatic measurements (not part of previous B14024 release)

OSA

Improvements

- Improved handling of the OSA deactivation

FiberComplete

New functionalities

- For IL/ORL referencing, addition of default reference softkey [Init Ref]
- Integration of the automated OEO bidirectional OTDR acquisition when bi-directional OTDR licence and datalink available

Improvements

- Enhanced data communication between modules
- Management of FiberComplete function activation when the remote unit is set to OTDR source mode
- Improved FiberComplete sequence (not part of previous B14024 release)

Scope

Improvements

- Improvement of the fiber number editor as well as the profile edition
- Improved management of the setup menu when going from Setup to Results and back to Setup

Script

New functionalities

- Management of OEO function